



MANIFOLD MOUNTING OF VALVES WITH MULTI-PIN CONNECTION

S E R I E S



Manifold mounting of valves with multi-pin connection

series S8

DESCRIPTION


The series "S8" is the new family of solenoid valves mounted on manifold bases whose integrated electrical part is capable of handling up to 32 signals thanks to the multi-pin connection. The valves belonging to this series are characterized by compact overall dimensions, high flow-rate and by a very smart engineering process resulted in just a few components needed for the assembly. The reduced overall dimensions allow to assembly the manifold both in a "vertical" or "horizontal" position, depending from the different mounting requirements. This series of valves comes with all the pneumatic functions requested by the market, including the "2x2/2" and "2x3/2" versions. They can comply with ATEX directive, 3GD category, upon request.

TECHNICAL DATA	
Operating pressure (port 1, 3 and 5)	-1 ÷ 8 bar
Piloting pressure (port 12/14)	2.5 ÷ 7 bar
Working temperature	0 ÷ 50 °C
Fluid	Compressed air, filtered, continuous lubricated, unlubricated or dry lubricated
Air purity class	Class 3-4-3 to ISO 8573-1 standard
Port size	Inlet & exhaust port on input module: G1/4; Inlet & exhaust port on intermediate bases: G1/8; Outlet lines: G1/8; Supply & exhaust port on piloting valves: M5
Protection class	IP 65 to EN 60529
Voltage	24 VDC ±10%
Single solenoid consumption	1,44 W (60 mA)
Duty cycle	Continuous rating ED100%
Max No. of solenoids	22 with a 25-pins sub-D plug 32 with a 37-pins sub-D plug




MATERIALS		
Bottoms	Techno-polymer	
Body	Cast painted aluminium alloy	
Distance ring	Acetal resin - brass	
Spools	Nickel-plated steel	
Springs	Stainless steel	
Pistons	Anodized alluminium alloy	
Seals	NBR rubber	
Manifold	Techno-polymer	
Tie-rods	Stainless steel	

FLOW CHART




PILOTING CHART



series

ORDER KEY FOR MANIFOLD MOUNTING IN THE MULTI-PIN CONNECTION VERSION



MANUAL ACTUATOR OF PILOTING SOLENOID VALVES

M Monostable

ELECTRICAL CONNECTION

D25 Sub-D 25 pins **D37** Sub-D 37 pins

INLET OF PILOTING SOLENOID VALVE

D Internal I External

SOLENOID VALVES/BASES ARRANGEMENT*

A 5/2 Monostable

B 5/2 Bistable E 3/2 N.O. + 3/2 N.O.

C 5/3 Closed centre **F** 3/2 N.C. + 3/2 N.C.

G 3/2 N.C. + 3/2 N.O.

H 2/2 N.O. + 2/2 N.O.

I 2/2 N.C. + 2/2 N.C.

L 2/2 N.C. + 2/2 N.O.

 $\boldsymbol{\mathsf{M}}$ Intermediate base with through ducts

N Intermediate base with duct "1" closed

O Intermediate base with ducts "1", "3" and "5" closed

P Intermediate base with ducts "3" and "5" closed

Q Monostable base with closing plate (fit for mounting the S8A valve)

R Bistable base with closing plate (fit for mounting the S8B, SBC, S8E

S8F, S8G, S8H, S8I, S8L)

TERMINAL MODULE

T Blind terminal module

ATEX

/EX Consistent with the ATEX directive



II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc


ORDER EXAMPLE


Manifold mounting with input module with sub-D 25 pins plug and internal inlet.

Monostable actuator of the piloting solenoid valve.

Solenoid valves and intermediate bases arrangement (starting from the input module):

- 1 5/2 Monostable
- 2 5/2 Monostable
- 3 5/2 Bistable
- 4 3/2 N.C. + 3/2 N.C.
- 5 3/2 N.C. + 3/2 N.C.
- 6 Intermediate base with through ducts







^{*} NB: When there are same and consecutive types, indicate at first the letter referring to the solenoid valves/bases and then the number stating how many of them must be assembled consecutively. For example: S8MD25D/AAAFFFFGG becomes S8MD25D/A3F4G2

ORDER EXAMPLE

Manifold mounting with input module with sub-D 37 pins plug and external inlet. Monostable actuator of the piloting solenoid valve. Solenoid valves and intermediate bases arrangement (starting from the input module): 1 5/2 Monostable 2 5/2 Monostable 3 5/2 Bistable В 4 Intermediate base with ducts 1, 3 & 5 closed 5 5/3 Closed centre 6 5/3 Closed centre A2BOC2 Series Manual actuator


Electrical connection Inlet of piloting solenoid valve Solenoid valves/bases arrangement

Terminal module -

ATEX -


ORDER EXAMPLE Manifold mounting with input module with sub-D 37 pins plug and internal inlet. Monostable actuator of the piloting solenoid valve. Solenoid valves and intermediate bases arrangement (starting from the input module): 1 5/2 Monostable 2 5/2 Monostable 3 5/2 Monostable 4 5/2 Monostable 5 5/2 Monostable 6 5/2 Monostable D37 D Series Manual actuator Electrical connection Inlet of piloting solenoid valve Solenoid valves/bases arrangement Terminal module -ATEX -

PARTS LIST



1	Tightening screws
2	Tie-rods
3	Junction nipple for odd stations or to add a station
4	Valve with pneumatic function type "A" (5/2 monostable)
5	Valve with pneumatic functions type "B", "C", "E", "F", "G", "H", "I", "L"
6	Modular base with single solenoid for 5/2 monostable valve ("A")
7	Modular base with for valves type "B", "C", "E", "F", "G", "H", "I", "L"
8	Intermediate modular base with auxiliary inlets/exhausts
9	Input module
10	Terminal module

INPUT MODULE WITH INTERNAL INLET FOR PILOTING SOLENOID VALVES - SBTD ...




/EX Consistent with the ATEX directive



II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc

E.G.: **S8TD37/EX**

INPUT MODULE WITH EXTERNAL INLET FOR PILOTING SOLENOID VALVES - SBTI...



/EX Consistent with the ATEX directive



II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc

E.G.: **S8TI37/EX**

PNEUMATIC FUNCTIONS*

Symbol	Function	Response time at 6 bar (ms)		Flow rate	Weight	TYPE
- ,		Pilot	Return	(NI/min)	(g)	
14 5 3 12	5/2 monostable	Solenoid (13)	Pneumomechanical spring (38)	750	106	S8A
14 5 3 112	5/2 bistable	Solenoid (11)	Solenoid (11)	750	136	S8B
4 2 14 5 3 12	5/3 closed center	Solenoid (15)	Solenoid (17)	600	146	S8C
14 15 1 3 112	3/2 N.O.+3/2 N.O. = 5/3 pressure centre	Solenoid (15)	Solenoid (17)	600	146	S8E
14 5 1 3 12	3/2 N.C.+3/2 N.C. = 5/3 open centre	Solenoid (15)	Solenoid (17)	600	146	S8F
14 5 1 3 12	3/2 N.C. + 3/2 N.O.	Solenoid (15)	Solenoid (17)	600	146	S8G
14 11 12	2/2 N.O. + 2/2 N.O.	Solenoid (15)	Solenoid (17)	600	146	S8H
114 11 12	2/2 N.C. + 2/2 N.C.	Solenoid (15)	Solenoid (17)	600	146	S8I
114	2/2 N.C. + 2/2 N.O.	Solenoid (15)	Solenoid (17)	600	146	S8L

*Please contact our sales dpt. for the 2/2 + 3/2 pneumatic function




/EX Consistent with the ATEX directive


II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc

E.G.: **S8F/EX**

VALVE DIMENSIONS




BLANKING PLATE - KIT/PC/S8







MODULAR BASE WITH SINGLE SOLENOID VALVE AND MONOSTABLE MANUAL ACTUATOR - S81M




/EX Consistent with the ATEX directive



II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc

E.G.: **S81M/EX**

MODULAR BASE WITH DOUBLE SOLENOID VALVE AND MONOSTABLE MANUAL ACTUATOR - S82M



 $\ensuremath{\text{/\text{EX}}}$ Consistent with the ATEX directive




II 3G c Ex nA IIC T5 Gc -5°C≤Ta≤50°C II 3D c Ex tc IIIC T100°C IP65 Dc


E.G.: **S81M/EX**



INTERMEDIATE BASE WITH AUXILIARY INLETS AND EXHAUSTS - S8M, S8N, S8O, S8P




TERMINAL MODULE - S8TC





TIE RODS FOR MANIFOLD (PAIR) - S8-T...

TYPE	No. OF STATIONS	WHEIGHT (g)
S8-T2	2	24
S8-T4	4	42
S8-T6	6	60
S8-T8	8	78
S8-T10	10	96
S8-T12	12	114
S8-T14	14	132
S8-T16	16	150
S8-T18	18	168
S8-T20	20	186
S8-T22	22	204
S8-T24	24	222
S8-T26	26	240
S8-T28	28	258
S8-T30	30	276



PAIR OF NIPPLES FOR ADD ONE, THREE OR FOUR STATIONS





This nipple allows to add a valve station at the end of the manifold, and it's possible to use two or more nipples consecutively

HOW TO CHOOSE THE RIGHT TIE-RODS & NIPPLES

Manifold of 16 stations: use the "S8-T16" tie-rod (16).



Manifold of 17 stations: "S8-T16" tie-rod + "S8-N1" nipple (16+1).




Manifold of 34 stations: "S8-T30" tie-rod + "S8-4" nipple . (30+4)




Manifold of 37 stations: "S8-T30" tie-rod + "S8-3" & "S8-4" nipples. (30+3+4)




OVERALL DIMENSIONS




STANDARD HORIZONTAL FIXING




STANDARD VERTICAL FIXING



VERTICAL FIXING THROUGH FEET - S8/FP



VERTICAL FIXING ONTO DIN RAIL - S8/FD



Manifold mounting of valves with multi-pin connection


DESCRIPTION


The electrical connection of the manifold of modular valves is automatically made during the assembly of the manifold using the PCBs with male / female connectors housed in each base. Once the manifold is assembled, the electrical components mounted in series are able to manage up to a maximum of 32 electrical signals.

The input module, equipped with 25-pins or 37-pins sub-D plug, defines the maximum number of manageable signals (respectively 22 signals for the input modules "S8TD25" & "S8TI25", and 32 signals for the modules "S8TD37" & "S8TI37").


Each piloting solenoid valve, including resistors and LEDs, requires about 1.44 W (60 mA) and the electrical circuit is disegned for not restrict the number of piloting solenoid valves that can be energized simultaneously in the manifold. Each solenoid is also equipped with a system which reduces the higher current peaks up to + 10% of the value of nominal voltage and which prevents the upstream return of the accumulated current that could damage sensitive electrical devices

The concept of housing the piloting solenoid valve on manifold greatly simplifies the production costs and consequently the spare parts become cheaper. This solution does not allow to use 5/2 monostable valves with a double solenoid base.







MULTI PIN CONNECTION WITH A MANIFOLD MADE OF ONLY SINGLE SOLENOID BASES



MULTI-PIN CONNECTION WITH A MANIFOLD MADE OF ONLY DOUBLE SOLENOID BASES




MULTI-PIN CONNECTION WITH A MIXED MANIFOLD MADE OF BOTH SINGLE & DOUBLE SOLENOID BASES AND A INTERMEDIATE BASE




Manifold mounting of valves with multi-pin connection

ORDER EXAMPLE OF A MULTI-PIN PNEUMATIC & SOLENOID CONNECTION
OF A MIXED MANIFOLD MADE OF: No. 2 SINGLE SOLENOID BASES, No.7 DOUBLE SOLENOID BASES AND No.2 INTERMEDIATE BASES



In this example we can see how the two intermediate bases "O" (S80), having the ducts "1", "3" and "5" interrupted, create three zones with independent pressure in the manifold, thus meaning that the common supply pressure of the valves in positions 1, 2 and 3, may be different from one of the valves in positions 5, 6 and 7 and which is even different from the common supply pressure of the valves in positions 9, 10 and 11 but all the valves are still electrically communicating on the same manifold. In all the three zones the external inlet for piloting solenoid valves line, determined by the chosen input module, is in common, so that the pressure in the duct must be properly sized for the correct fuctioning of the valves. For example: if the first zone works at -1 bar, the second at 2 bar and the third at 6 bar, the piloting pressure must be at least 3.5 bar. See piloting chart on page 3.

IN-LINE SUB-D FEMALE PLUGS



CODE	TYPE	Α	B (m)	WEIGHT (g)
MEV/CF3	Sub-D 25	55,5	3	170
MEV/CF5	Sub-D 25	55,5	5	410
MEV/CF10	Sub-D 25	55,5	10	760
MEV/37CF5	Sub-D 37	72,5	5	450
MEV/37CF10	Sub-D 37	72,5	10	800





